

# PEEL STRENGTH TESTING

**EN 868-5 Directive** specifies the controls to be run on the pouch and defines test methods to be run on the heat seal joint of pouches and packaging reels

Using a calibrated dedicated machinery, Gandus Saldatrici can provide you with a Peel Strength Test of the seal, ensuring compliance with EN 868-5 requirements and to Validation process Qualification Performance (QP).


Please feel free to ask for technical advice.



## REPORT TEAR AND PEEL TEST

DATE	TIME	SEALER	SERIAL N°
18/11/2013	9:20:45	Medical H460 ATDP	0496

TEST	WIDTH STRIP	PROPAGATION SPEED	MAX LOAD
A30	15.0 mm	200.0 mm/min	3.86 N



This report was produced using NEXYGEN from Lloyd Instruments Ltd



**...because we support users in their daily work,  
 surrounding them with the highest level of safety**